

[See all 78 Products in Family](#)

Preloaded Norland Optical Adhesive NOA 165H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#17-383** **2 In Stock**

-

1

+

₹3,488

ADD TO CART

Volume Pricing	
Qty 1-4	₹3,488 each
Qty 5+	₹3,285 each
Need More?	Request Quote

Product Downloads

General	
0.34	Size (oz):
165H	Norland Number:
4 months	Shelf Life:
Barrel	Type:

	Typical Applications:
Bonding glass to glass	
	Note:
Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.	

Optical Properties	
	Index of Refraction (n _d):
1.65	
	Absorption Range (nm):
315 - 450	

Material Properties	
	Glass Bonding:
Excellent	
	Metal Bonding:
Excellent	
	Plastic Bonding:
Excellent	
	Viscosity (cps):
200 - 300	
	Bonding Type:
Glass to Glass	
	Energy for Full Cure (J/cm ²):
6	

Environmental & Durability Factors	
	Durability:
Soft & Flexible	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 251:
Compliant	
	Country of Origin:
United States	
	Imported By:
Edmund Optics India Private Limited	

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- [Applicator and Bulk Bottles](#) of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as MIL-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.
