

Programmable 3-Axis Joystick Controller

See More by [Zaber™](#)



Programmable 3-Axis Joystick Controller, #15-293

Stock **#15-293** 1 In Stock

-

1

+

₹79,650

ADD TO CART

Volume Pricing	
Qty 1+	₹79,650 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Manual Control:
3-axis joystick, 8 programmable keys

Note:
Requires a 24-48 VDC power supply for operation.
A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control.

Physical & Mechanical Properties

160 x 120 x 96	Dimensions (mm):
0.52	Weight (kg):
Electrical	
Locking 4-pin M8	Device Interface:
50	Maximum Operating Current (mA):
Hardware & Interface Connectivity	
Power Supply: Not included, see the Accessories tab for recommended 24 to 48V Power Supply & Tech Info tab for connector information.	
RS-232	Computer Interface:
Environmental & Durability Factors	
0 - 50	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

PRODUCT DETAILS

- Can Control Up to 3 Independent Axes
- Intuitive Interface with Computer-Driven or Manual Operation
- Fully Programmable Buttons, Velocity Profile, and Sensitivity
- Power Supply and Data Cable Sold as Separate Accessories

The Zaber Programmable Joystick Controller can be connected in series to up to three independent Zaber motors. In standalone operation, the Zaber Programmable Joystick Cotroller is ideal for simple, two to three axis movement, and is aided by key switches that are preprogrammed with commands to home, save current position, and go to saved position. All eight key switches are fully programmable to send any arbitrary command to each axis or to trigger the computer to send command sequences. The analog axis settings include programmable velocity, velocity profile, invert, and unit number, and calibration for the limits and deadband.

TECHNICAL INFORMATION


Device Overview / Connectors

Images are shown looking into the device.

Power

1

2



Pin	Description
1	24 - 48 V
2	GND (Note: power supplies ground this pin to AC Earth)

Note: To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.