

[See all 7 Products in Family](#)

Reflection Probe Tip Adapter

See More by [Ocean Optics](#)



Stock #90-568 **NEW** 1 In Stock

⊖ 1 ⊕ MRP ₹41,630

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹41,630 each
Need More?	Request Quote

Product Downloads

General

Type:
Reflection probe holder – Adapter for 1/4" (6.35 mm) and 1.8" (3.17 mm) diameter reflection probes

Model Number:
RPH-ADP

Regulatory Compliance

[Compliant](#)

RoHS 2015:

Certificate of Conformance:

[View](#)

Reach 250:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Versatile Sampling for Diffuse/Specular Reflectance, Backscatter & Fluorescence
- Various Wavelength and Environmental Durability Models
- Extreme Solarization-Resistant (XSR) Probe Features Ultra-Low Loss Fiber for Harsh UV Exposure
- Connects Directly with Ocean Optics Spectrometers & Accessories

Ocean Optics Reflection/Backscatter Probes are compact, fiber-coupled sampling tools for measuring diffuse and specular reflectance, backscatter, or fluorescence in solids, solutions, or powders, and connect directly with [Ocean Optics Spectrometers and Accessories](#). They provide quantitative insights into a sample's color, appearance, and chemical composition. Choose from Visible-NIR, Solarization-Resistant, or XSR models for applications ranging from routine reflectance to demanding UV measurements. With durable jacketing, precision ferrules, and solarization-resistant fiber, the rugged design ensures reliable performance even in harsh conditions. Ocean Optics Reflection/Backscatter Probes can be optimized for UV applications, with the XSR probe featuring ultra-low loss fiber designed to withstand harsh UV exposure.
