

RS-232 Serial Port Adapter

See More by [Zaber™](#)



#59-749: RS-232 Serial Port Adapter

Stock **#59-749** **1 In Stock**

-

1

+

MRP ₹1,335

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,335 each
Need More?	Request Quote

Product Downloads

General	
Cables & Power Supplies	Type:
6-pin Mini-Din to RS-232 Serial Port Adapter	Note:

Regulatory Compliance	
Compliant	RoHS 2015:

Certificate of Conformance:	
View	
Reach 247:	
Compliant	
Country of Origin:	
China	
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Product Details

- Miniature, Robust Design
 - Integrated Motor and Controller
 - Controlled Manually or via RS-232 Serial Interface
 - Available with Integrated, 250 Counts per Revolution (CPR) Motor Mounted Encoder
- Zaber™ High Accuracy Linear Actuators feature 50nm resolution with up to 50mm travel distance. These computer-controlled, self-contained linear actuators include a stepper motor and a built-in controller that can connect directly a computer's RS-232 port while requiring only the included 15V power supply. Encoder versions are available for all travel lengths and include 250 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ High Accuracy Linear Actuators also feature an industry standard 3/8" shank that fits most common stages. The actuator shaft does not rotate and will not transmit any torque to the translation stage. When used manually, the actuator can be monitored using a computer if needed.
- Note:** A 6ft. data cable, RS-232 adapter, and universal power supply are sold separately as accessories