

[See all 15 Products in Family](#)

# SCHOTT NG4 785nm 50mm Sq., 1.0 OD ND Filter

See More by [SCHOTT Optical Components](#)



Stock #21-378 **3 In Stock**

MRP ₹19,472

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹19,472 each
Qty 10-25	₹17,455 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Type: Neutral Density Filter

### Physical & Mechanical Properties

Dimensions (mm): 50.0 x 50.0 ±0.2

Clear Aperture CA (mm): 48.5 x 48.5

2.44 (nominal)	<b>Thickness (mm):</b>
≤3	<b>Parallelism (arcmin):</b>
Fine Ground	<b>Edges:</b>
0.5 x 45°	<b>Bevel:</b>
Plano	<b>Shape of Back Surface:</b>

## Optical Properties

1.0 ± 0.023 at Calibrated Wavelength	<b>Optical Density OD (Average):</b>
785	<b>Design Wavelength DWL (nm):</b>
SCHOTT NG4	<b>Glass/Filter Number:</b>
Uncoated	<b>Coating:</b>
60-40	<b>Surface Quality:</b>
10 ± 1.06 at Calibrated Wavelength	<b>Transmission (%):</b>

## Material Properties

470	<b>Transformation Temperature (°C):</b>
-----	---

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Malaysia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000	<b>Imported By:</b>

## Product Details

- Calibrated for Specific Wavelengths
- Optical Densities Ranging from 0.3 to 3.0
- NG3, NG4, NG5, NG9, or NG11 Glass Types

SCHOTT Calibrated Neutral Density (ND) Filters are tested and calibrated to a precision optical density tolerance at either 405nm, or 633nm, or 785nm. Manufactured from NG3, NG4, NG5, NG9, or NG11 SCHOTT Glass, the filters are ideal for providing precise attenuation at common laser wavelengths. Available in optical densities ranging from 0.3 to 3.0, these filters can be integrated into a variety of optical systems and experiments. SCHOTT Calibrated Neutral Density (ND) Filters are available in a standard 50 x 50mm size and multiple filters can be stacked to achieve custom optical densities. The measured OD value for each filter at the specified wavelength is referenced on the box.

**Note:** Please contact us if your application requires a custom size SCHOTT Calibrated Neutral Density (ND) Filter.

**Quote Your Size**