

TECHSPEC[®] SilverTL Series High Magnification Kit



SilverTL[™] Telecentric Lenses



Stock **#29-137** [CONTACT US](#)

-

1

+

₹2,28,162

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,28,162 each
Need More?	Request Quote

Product Downloads

General

Contents of Kit:

- 4.0X Silver Series: 58-432
- 2.0X Silver Series: 58-431
- 1.0X Silver Series: 58-430
- 0.75X Silver Series: 67-731

Optical Properties

Working Distance (mm):

4.0X Silver Series: 44

2.0X Silver Series: 75
1.0X Silver Series: 83
0.75X Silver Series: 100

f/6 - f/22

Aperture (f/#):

Sensor

2/3"

Maximum Sensor Format:

Regulatory Compliance

View

Certificate of Conformance:

China

Country of Origin:

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

• Easy to Order Kits of Our Best Selling Telecentric Imaging Lenses

• Various Magnification and Working Distance Kits Available

• TECHSPEC [SilverTL](#), [VariMagTL](#), and [CompactTL](#)

TECHSPEC® Telecentric Imaging Lens Kits provide sets of TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring telecentric lenses including machine vision, metrology, automotive and electronic inspection, measurement, and gauging. TECHSPEC® Telecentric Imaging Lens Kits offer various selections of magnifications and working distances within the product lines. The TECHSPEC® [SilverTL](#), [VariMagTL](#), and [CompactTL](#) lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- [SilverTL](#): Silver Telecentric, Metrology and Gauging
- [VariMagTL](#): Variable Magnification Telecentric, Adjustable Magnification That Can Be Locked with a Set Screw
- [CompactTL](#): Compact Telecentric, C-Mount Lenses for Machine Vision, Factory Floors, Assembly Lines