


## Single Ended, FET Variable Voltage Amplifier



Stock #90-637 NEW 2 In Stock

1 + - MRP ₹2,34,171

i Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,34,171 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### Cut-Off Frequency (Hz):

Lower: DC/1.5  
Upper: 10

### General

#### Remote Control:

Yes

#### Note:

Includes:  
LEMO® 3-pin connector  
Datasheet

### Electrical

5 x 10<sup>-9</sup> Voltage Noise, High Gain (V/Hz<sup>1/2</sup>):

20/40/60/80(Switchable) Gain (dB):

1 x 10<sup>6</sup> Input Impedance (kΩ):

## Hardware & Interface Connectivity

±10 V (@ 100 kΩ Load) Output Voltage (V):

Power Supply:  
Power Supply Required and Sold Separately.  
USA: [#59-180](#)  
Europe: [#59-180](#)  
Japan: Not Available  
Korea: Not Available  
China: [#59-180](#)

50 Ω, BNC Output Type:

1 TΩ, BNC Input Type:

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

Germany Country of Origin:

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91-80-6845 0000

## Product Details

- High-Precision, Low-Frequency Signal Amplification with Constant Bandwidth Performance
- Low DC Offset Drift for Long-Term Measurement Stability
- AC/DC Coupling Options

Low-Frequency Voltage Amplifiers provide variable amplification of DC to 100kHz signals, allowing precise control over signal gain in sensitive measurement applications. Their low-noise design and wide gain range preserve signal fidelity across amplification settings, ensuring accurate voltage measurements even at high gain. By maintaining stable performance with minimal DC offset drift, these amplifiers improve measurement clarity, repeatability, and reliability in demanding laboratory and industrial settings. Low-Frequency Voltage Amplifiers feature switchable AC/DC coupling and remote control capability, providing flexibility for integration into automated systems or standalone setups. These amplifiers are ideal for sensor readout, low-level signal detection, and precise data acquisition across a wide range of scientific and engineering applications.

**Note:** Power supply sold separately. Please see specifications for more details.