

[See all 9 Products in Family](#)

SMA Slit Adapter (for use with single core fibers)



SMA Slit Adapter

Stock #56-256 **5 In Stock**

MRP ₹20,178

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-4	₹20,178 each
Qty 5-9	₹18,054 each
Qty 10+	₹15,134 each
Need More?	Request Quote

Product Downloads

General

Note:
Converts the entrance and/or exit slit ports to accept SMA905 compatible optical fiber assemblies.

Regulatory Compliance

Compliant

RoHS 2015:

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

Note: Slit Adapter converts slit aperture to SMA connector compatible with Amphenol 906 series fiber optic connectors.

- 6 Choices of Wavelength Ranges
- Compact, Handheld Size
- 2 NIR Versions

Manual Mini-Chrom Monochromators are manually operated monochromators that utilize a knob dial for wavelength selection. Rotation of the dial causes, via a precision lead screw/sine bar mechanism, rotation of the diffraction grating which positions the selected wavelength at the exit slit. Wavelength is read directly in nanometers (nm) from a four digit counter on all models. Manual Mini-Chrom Monochromators near infrared Models E and F require the micrometer reading to be doubled, to 2nm per division, for wavelength selection and readout. #56-253 and #56-254 have gold coated optics for maximum grating efficiency and superior reflectance in the near infrared.

Note: Dialing the monochromators outside of their spectral ranges may cause a mechanical error. Be sure to only use the monochromators within their specified range.

These are ideal as components for system integration; all that is required is the light source and sensor. A set of 300 micron slits is included. Narrower slits increase resolution but decrease throughput. Wider slits increase throughput at the expense of spectral purity. These instruments are designed for use in research, quality control, and teaching. They are also used extensively as components in a variety of sophisticated analytical and biomedical equipment such as: clinical chemistry analyzers, HPLC detectors, and UV-VIS-NIR spectrophotometers. The Mini-Chrom is a compact, in-line Fastie-Ebert design with throughput, resolution, stray light, and power handling features comparable to many larger, more expensive, conventional models.

Technical Information

