

[See all 10 Products in Family](#)

## SMO 30° Single Element Lens



Single Element Lens

Stock #90-760 **NEW** 20+ In Stock

⊖ 1 ⊕ MRP ₹958

📌 Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1-9	₹958 each
Qty 10-24	₹815 each
Qty 25-49	₹767 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Clamp-ring soldered **Note:**

### Physical & Mechanical Properties

10.50 **Diameter (mm):**

**Height (mm):**

6.42mm

## Optical Properties

**Substrate:**

SILASTIC™ MS-1002 Moldable Silicone

**Color:**

White

**Overall Efficiency (%):**

0.89

## Regulatory Compliance

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Five Lens Shape Options
- Over 90% Efficient from UV-A through Visible and Near IR
- Solder Pads Allow for High-Precision Placement

LumenFlow Surface Mount Optics deliver high optical efficiency in a compact, low-profile package that easily integrates into photonic assemblies. Molded with tight tolerances, each optic ensures repeatable performance across production batches. Designed for automated placement and soldering on a PCB simultaneously with SMT components, these optics support high-volume manufacturing workflows while reducing assembly costs and cycle times. LumenFlow Surface-Mount Optics are made with optical grade silicone which doesn't melt or reflow and has an operating temperature of 200C. Silicone is also water resistant, submersible, UV resistant, and resists impact and environmental wear, ensuring long-term stability in demanding applications. Available in a broad range of focal lengths, and form factors, these optics meet the needs of diverse machine-vision, sensing and illumination applications from UV-A to 1.6µm.

## Technical Information

- 
- 
- 
- 
-