

SWIR 1450nm Adjustable Ring Light



Efflux SWIR LED Ring Lights

Stock #28-625 [CONTACT US](#)

1 [-](#) [+](#) MRP ₹4,24,421

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹4,24,421 each
Need More?	Request Quote

Product Downloads

General

Model Number:
EFFI-RING-1450-KIT-CW

Number of LEDs:
-

Type of Illumination:
LED Illuminator

Uniformity (%):
>90%

Manufacturer:

Effilux

Ring Light

Geometry:

Strobed or Constant

Illumination Mode:

Physical & Mechanical Properties

58.0

Inner Diameter (mm):

151.0 W x 117.0 L x 40.0 H

Dimensions (mm):

400

Weight (g):

100 x 100

Active Area (mm):

Optical Properties

SWIR

Color:

1,450

Wavelength (nm):

Hardware & Interface Connectivity

M12, 5 pins

Connector:

24VDC

Input Voltage (V):

Threading & Mounting

M4 (x4) and 3.5mm Thru (x4)

Mount:

Environmental & Durability Factors

-10 to 50

Operating Temperature (°C):

IP65

Environmental Rating:

Regulatory Compliance

[View](#)

Certificate of Conformance:

France

Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Adjustable Illumination Angles

Effilux SWIR LED Ring Lights provide intense and uniform lighting for machine vision, sorting and silicon inspection applications. Available in wavelengths of 1050, 1200, 1300, 1450, 1550, and 1650nm. These ring lights feature adjustable lens positions and illumination angles for added flexibility. Effilux SWIR LED Ring Lights are ideal complements for applications utilizing TECHSPEC® C Series Fixed Focal Length SWIR Lenses, TECHSPEC® SilverTL™ SWIR Telecentric Lenses and LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) SWIR Cameras or Teledyne FLIR IIS Forge 1GigE SWIR Cameras.

Note: Included with the ring lights are one semi diffuse window and one 25° lens position kit.

3D-Printable Mount Files



Ring Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to ¼-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications

[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#) 