

[See all 22 Products in Family](#)

TECHSPEC[®] C Series Kit



C Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock **#25-606** [CONTACT US](#)

-

1

+

₹78,300

ADD TO CART

Volume Pricing	
Qty 1+	₹78,300 each
Need More?	Request Quote

Product Downloads

General	
Series:	
C Series	
Contents of Kit:	
8.5mm C Series: 58-000 12mm C Series: 58-001 16mm C Series: 59-870 25mm C Series: 59-871 35mm C Series: 59-872	
Optical Properties	

8.5mm C Series: 100 - ∞	Working Distance (mm):
12mm C Series: 100 - ∞	
16mm C Series: 100 - ∞	
25mm C Series: 100 - ∞	
35mm C Series: 165 - ∞	
Aperture (f/#):	
8.5mm C Series: f/1.3 - f/16	
12mm C Series: f/1.8 - f/16	
16mm C Series: f/1.6 - f/16	
25mm C Series: f/1.4 - f/16	
35mm C Series: f/1.65 - f/22	

Sensor

8.5mm C Series: 2/3"	Maximum Sensor Format:
12mm C Series: 2/3"	
16mm C Series: 2/3"	
25mm C Series: 2/3"	
35mm C Series: 2/3"	

Regulatory Compliance

[View](#) Certificate of Conformance:

Country of Origin:	
United States	

Edmund Optics India Private Limited	Imported By:
-------------------------------------	--------------

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC **C**, **UC**, and **HP** Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- **C Series:** Compact (C), FA Lenses for Machine Vision
- **UC Series:** Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- **HP Series:** High Performance (HP), C-Mount Lenses for Machine Vision