

**TECHSPEC® UC Series Expanded Kit**



UC Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock #25-609 [CONTACT US](#)

- 1 + MRP ₹1,75,837

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,75,837 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

UC Series **Product Family:**

- Contents of Kit:**
- 4mm UC Series: [33-300](#)
  - 6mm UC Series: [33-301](#)
  - 8mm UC Series: [33-307](#)
  - 12mm UC Series: [33-303](#)
  - 16mm UC Series: [33-304](#)
  - 25mm UC Series: [33-305](#)
  - 35mm UC Series: [33-306](#)

## Optical Properties

### Working Distance (mm):

4mm UC Series: 0 - ∞  
6mm UC Series: 50 - ∞  
8mm UC Series: 50 - ∞  
12mm UC Series: 100 - ∞  
16mm UC Series: 200 - ∞  
25mm UC Series: 200 - ∞  
35mm UC Series: 200 - ∞

### Aperture (f/#):

4mm UC Series: f/1.8 - f/11  
6mm UC Series: f/1.85 - f/11  
8mm UC Series: f/1.8 - f/11  
12mm UC Series: f/1.8 - f/11  
16mm UC Series: f/1.8 - f/11  
25mm UC Series: f/1.85 - f/16  
35mm UC Series: f/1.85 - f/16

## Sensor

### Maximum Sensor Format:

4mm UC Series: 1/2"  
6mm UC Series: 1/2"  
8mm UC Series: 1/2"  
12mm UC Series: 1/1.8"  
16mm UC Series: 1/1.8"  
25mm UC Series: 1/1.8"  
35mm UC Series: 1/1.8"

## Regulatory Compliance

### Certificate of Conformance:

[View](#)

### Country of Origin:

United States

### Imported By:

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
- Full Product Line or Select Focal Lengths Kit Versions Available
- TECHSPEC **C**, **UC**, and **HP** Imaging Lenses are Also Sold Individually

TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.

- **C Series:** Compact (C), FALenses for Machine Vision
- **UC Series:** Ultra-Compact (UC), High Resolution Lenses for Small Sensors
- **HP Series:** High Performance (HP), C-Mount Lenses for Machine Vision