

[See all 10 Products in Family](#)

Teledyne Dalsa Xtium2-CXP6 PX8 Quad Frame Grabber

See More by [Teledyne DALSA](#)



Stock #91-737 **NEW** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹2,25,250

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | ₹2,25,250 each |
| Need More? | Request Quote |

Product Downloads

General

OR-A8X6-XPX40 **Model Number:**
Teledyne DALSA **Manufacturer:**

Sensor

2GB **Image Buffer:**
Mono: 8, 10, 12, 14 and 16-bit; RGB: 8, 10 or 12- **Pixel Depth:**

Hardware & Interface Connectivity

CoaXPress **Interface:**

PCIe Gen3 x8 slot **Computer Interface:**

4 Port (4 Cameras) **Ports:**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High Data Throughput with Reliable, Low-Latency Image Transfer
- Minimizes CPU Usage and Improves Processing Times
- High Performance for Camera Link®, Camera Link® HS, GigE, and CoaXPress® Interface Standards

Teledyne DALSA Frame Grabbers provide high-performance image acquisition solutions for demanding machine vision and industrial imaging applications. Designed to support a wide range of camera interface standards and data rates, these frame grabbers deliver reliable, high-bandwidth image transfer with low latency. Advanced onboard processing capabilities and robust driver support simplify system integration while maximizing throughput. Teledyne DALSA Frame Grabbers are engineered for seamless compatibility with cameras from a wide range of manufacturers, enabling flexible deployment across diverse imaging platforms. With scalable configurations optimized for Camera Link, Camera Link HS, GigE, CoaXPress, and other leading interfaces, they provide an ideal solution for high-speed, high-resolution imaging environments. Frame Grabbers are specialized capture boards focused on capturing individual, high-resolution, or non-standard frames for machine vision applications.