

[See all 10 Products in Family](#)

# Teledyne Dalsa Xtium2-XGV Dual Frame Grabber

See More by [Teledyne DALSA](#)



Stock #91-742 NEW **1 In Stock**

MRP ₹1,33,281

Price inclusive of all taxes

ADD TO CART

#### Volume Pricing

Qty 1+	₹1,33,281 each
Need More?	<a href="#">Request Quote</a>

#### Product Downloads

#### General

OR-A8G0-PXF20 **Model Number:**  
Teledyne DALSA **Manufacturer:**

#### Sensor

2GB **Image Buffer:**  
Mono: 8, 10, 12, 14 and 16-bit; RGB: 8, 10 or 12- **Pixel Depth:**

## Hardware & Interface Connectivity

GigE Vision **Interface:**

PCIe Gen3 x8 slot **Computer Interface:**

2 Port (32 Cameras) **Ports:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- High Data Throughput with Reliable, Low-Latency Image Transfer
- Minimizes CPU Usage and Improves Processing Times
- High Performance for Camera Link®, Camera Link® HS, GigE, and CoaXPress® Interface Standards

Teledyne DALSA Frame Grabbers provide high-performance image acquisition solutions for demanding machine vision and industrial imaging applications. Designed to support a wide range of camera interface standards and data rates, these frame grabbers deliver reliable, high-bandwidth image transfer with low latency. Advanced onboard processing capabilities and robust driver support simplify system integration while maximizing throughput. Teledyne DALSA Frame Grabbers are engineered for seamless compatibility with cameras from a wide range of manufacturers, enabling flexible deployment across diverse imaging platforms. With scalable configurations optimized for Camera Link, Camera Link HS, GigE, CoaXPress, and other leading interfaces, they provide an ideal solution for high-speed, high-resolution imaging environments. Frame Grabbers are specialized capture boards focused on capturing individual, high-resolution, or non-standard frames for machine vision applications.