


[See all 22 Products in Family](#)

## Ultra-Thin Polarizer, 1310nm, 10 x 10mm, Uncoated



Ultra-Thin Polarizer, Square

Stock **#26-641** **1 In Stock**

MRP ₹45,704

**Price inclusive of all taxes**

**ADD TO CART**

Volume Pricing	
Qty 1+	₹45,704 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### Physical & Mechanical Properties

10 x 10 +0/-0.1      **Dimensions (mm):**

0.09 ± 0.025      **Thickness (mm):**

### Optical Properties

Uncoated      **Coating:**

>10,000:1      **Extinction Ratio:**

<b>Substrate:</b> □	
Sodium Silicate Glass Doped with Silver Nanoparticles	
<b>Surface Quality:</b>	
40-20	
<b>Transmission (%):</b>	
>87	
<b>Wavelength Range (nm):</b>	
1260 - 1360	
<b>Damage Threshold, By Design:</b> □	
10 W/cm <sup>2</sup>	
<b>Acceptance Angle (°):</b>	
± 20°	
<b>Transmitted Wavefront Error, RMS:</b>	
<3 λ	
<b>Environmental &amp; Durability Factors</b>	
<b>Operating Temperature (°C):</b>	
-50 to +400	
<b>Regulatory Compliance</b>	
<b>RoHS 2015:</b>	
<b>Compliant</b>	
<b>Certificate of Conformance:</b>	
<b>View</b>	
<b>REACH 241:</b>	
<b>Compliant</b>	
<b>Country of Origin:</b>	
Germany	
<b>Imported By:</b>	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- **NEW LOWER PRICE!**
- Lightweight 90µm Thick Substrate
- >10,000:1 Extinction Ratio
- Excellent Resistance to Temperature, Chemicals, and Harsh Environments
- Range of Standard Sizes, Coatings, and Custom Options Available

Ultra-Thin Nanoparticle Polarizers are a lightweight 90µm thick alternative to traditional polarizers while providing a high transmission and an extinction ratio of >10,000:1. Constructed from sodium silicate glass substrate doped with prolate silver nanoparticles, these polarizers provide high temperature stability up to +400°C, chemical resistance, and resistance to UV radiation and bleaching. These polarizers are available uncoated, Single-Side AR coated, or Double-Side AR coated and cover wavelength ranges from 366-1600nm. Ultra-Thin Nanoparticle Polarizers design are ideal for use in telecom, medical, and aerospace applications as well as in optical isolators, polarization interferometry, and improving signal-to-noise ratio.