

Ultra-Thin Polarizer, 1310nm, 25mm Dia, Double-Side AR Coated



Ultra-Thin Polarizer, Circle

Stock **#26-646** **3 In Stock**

-

1

+

MRP ₹2,17,419

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,17,419 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
25.00 +0/-0.2	Diameter (mm):
0.09 ± 0.025	Thickness (mm):
Optical Properties	
Double-Side AR	Coating:
>10,000:1	Extinction Ratio:

Substrate: ☐	
Sodium Silicate Glass Doped with Silver Nanoparticles	
Surface Quality:	
40-20	
Transmission (%):	
>95	
Coating Specification:	
Not available	
Wavelength Range (nm):	
1260 - 1360	
Damage Threshold, By Design: ☐	
10 W/cm ²	
Acceptance Angle (°):	
± 20°	
Transmitted Wavefront Error, RMS:	
<3 λ	

Environmental & Durability Factors

Operating Temperature (°C):	
-50 to +400	

Regulatory Compliance

RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
REACH 241:	
Compliant	
Country of Origin:	
Germany	
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- **NEW LOWER PRICE!**
- Lightweight 90µm Thick Substrate
- >10,000:1 Extinction Ratio
- Excellent Resistance to Temperature, Chemicals, and Harsh Environments
- Range of Standard Sizes, Coatings, and Custom Options Available

Ultra-Thin Nanoparticle Polarizers are a lightweight 90µm thick alternative to traditional polarizers while providing a high transmission and an extinction ratio of >10,000:1. Constructed from sodium silicate glass substrate doped with prolate silver nanoparticles, these polarizers provide high temperature stability up to +400°C, chemical resistance, and resistance to UV radiation and bleaching. These polarizers are available uncoated, Single-Side AR coated, or Double-Side AR coated and cover wavelength ranges from 366-1600nm. Ultra-Thin Nanoparticle Polarizers design are ideal for use in telecom, medical, and aerospace applications as well as in optical isolators, polarization interferometry, and improving signal-to-noise ratio.