

USB Motorized Filter Wheel



Mtorized Filter Wheels



Stock **#84-889** [CONTACT US](#)

-

1

+

₹90,587

ADD TO CART

Volume Pricing	
Qty 1+	₹90,587 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

- Type:

Adjustable - Rotary
- Type of Optics:

Circular

Filter Holder Response Time (seconds): 8-Position Filter Change: 0.8 8-Position Full Revolution: 2.1	
Optic Holding Style: #59-770 Required (for 1"/25mm) #59-783 Required (for 50mm)	

Motorized: Yes	
Type of Mount: Filter Wheel Housing, #59-770 or #59-783 Required	

Hardware & Interface Connectivity

Computer Interface: USB	
Control Interface: Internal; No Manual Hand Control	

Regulatory Compliance

RoHS 2015: Compliant	
Reach 224: Compliant	
Certificate of Conformance: View	

PRODUCT DETAILS

- USB or RS-232 Interface
- Bi-Directional Movement
- C-Mount and T-Mount Adapters Available

These Motorized Filter Wheels are ideal for a number of automated applications requiring spectral selection or light intensity control. The RS-232 filter wheel can be controlled directly via a control box, or remotely using an RS-232 interface. The USB filter wheel requires a PC connection for motorized operation. Both Motorized Filter Wheels include a Windows®-based graphical user interface, filter wheel housing with integrated stepper motor, USB or RS-232 cables, and 12VDC power supply.

Note: Filter holders are sold separately. Software and Manuals available for [download](#)

Two interchangeable filter holders are available for the Motorized Filter Wheels. The 8-position holder can accept up to eight 25mm and 1" diameter [filters](#) that are up to 5.5mm in thickness. The 5-position holder can accept up to five 50mm diameter filters that are up to 5.5mm in thickness. Each filter holder can be easily removed from the Motorized Filter Wheel without the use of tools. A hinged door is secured by a single captive thumbscrew; once opened, the filter holder can be extracted and another inserted in its place. The filter holders include an assortment of 0.75mm and 1.5mm thick spacers to accommodate different filter thicknesses. Each filter is held in place by two easily removable plastic tabs.

The filter wheel housing can be mounted using English or metric mounting plates. The English mounting plates are designed with three ¼-20 tapped holes for [post](#) mounting, and are compatible with English [laboratory tables](#). The metric mounting plates are designed with three M6 tapped holes for post mounting, and are compatible with metric laboratory tables. C-mount or T-mount adapters are available for easy integration.

The USB-to-serial converter allows USB connection of the RS-232 filter wheel's control box to a computer that does not have a native COM(RS-232) port.

TECHNICAL INFORMATION



