

UV-VIS Transmission Dip Probe

See More by [Ocean Optics](#)



Stock #90-570 **NEW** 1 In Stock

⊖ 1 ⊕ ₹1,10,925

ADD TO CART

Volume Pricing

Qty 1+	₹1,10,925 each
Need More?	Request Quote

Product Downloads

Fiber Connector Type:

SMA905

General

Model Number:

TP300-UV-MS

Note:

Breakout 1.5 meter from end of the probe

Optical Properties

Wavelength Range (nm):

200 - 1100

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 250:

United States

Country of Origin:

Edmund Optics India Private Limited

Imported By:

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV-VIS to VIS-NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).