

[See all 3 Products in Family](#)

TECHSPEC[®] VIS Coated, C-Mounted Non-Polarizing Cube Beamsplitter



C-Mounted Cube Beamsplitters

Stock **#49-682** **2 In Stock**

-

1

+

₹37,440

ADD TO CART

Volume Pricing	
Qty 1-4	₹37,440 each
Qty 5-9	₹30,330 each
Qty 10+	₹27,540 each
Need More?	Request Quote

Product Downloads

General

Type:
Non-Polarizing Beamsplitter

Type of Optics:
Non-Polarizing Cube Beamsplitter, VIS Coating

Beamsplitter Included:
[Non-Polarizing 50R/50T VIS Cube Beamsplitter](#)

Physical & Mechanical Properties

Cube	Construction:
38.0 x 38.0 x 50.0	Dimensions (mm):
38.0	Extension Length (mm):
Black Anodized Aluminum	Housing:
Optical Properties	
±2	Angle Tolerance (arcmin):
Faces: Multi-Layer Anti-Reflection for Visible Region	Coating:
50/50	Reflection/Transmission Ratio (R/T):
±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: □
40-20	Surface Quality:
430 - 670	Wavelength Range (nm):
1.25	Power (fringes) @ 632.8nm:
0.25	Irregularity (fringes) @ 632.8nm:
Threading & Mounting	
C-Mount Enclosure	Mount:
C-Mount (1" x 32 TPI)	Thread Type:
Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Simplifies Mounting and Alignment
 - Standard Female C-Mount Threaded Holes
 - Additional C-Mounted [Beamsplitters](#), [Filters](#), and [Mirrors](#) Available
- TECHSPEC® C-Mounted Cube Beamsplitters offer easy integration into systems, allowing the use of standard off-the-shelf components. The housing is 50mm H x 38mm W x 38mm D, with four C-Mount (1" x 32 TPI) female threaded apertures. A threaded aperture lid is included to close the unused port. The base has a centered 1/4-20 tapped hole for mounting to a post. The TECHSPEC® C-Mounted Standard Cube Beamsplitter features a coating for visible wavelengths and MgF2 anti-reflection coated faces.
- The C-Mounted Visible Non-Polarizing Cube Beamsplitter is designed for the 430 - 670nm wavelength range, and the C-Mounted NIR Non-Polarizing Cube Beamsplitter is designed for the 720 - 1080nm wavelength range.

Technical Information

