

[See all 22 Products in Family](#)

TECHSPEC[®] VIS NIR C Series Kit Expanded, C Mount



C Series: All lenses pictured may not be included in the kit. See "Contents of Kit" specification for included lenses.



Stock **#73-064** [CONTACT US](#)

-

1

+

MRP ₹2,71,262

 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,71,262 each
Need More?	Request Quote

Product Downloads

General	
C VIS-NIR Series	Product Family:
	Note: Filter thread adapter for 4.5mm and 6mm included

39-938 39-939 27-553	Contents of Kit:
--	-------------------------

27-554
67-714
67-715
67-716
67-717
87-425
85-308

Included Focal Lengths or Magnifications:
4.5,6,8.5,12,16,25,35,50

Optical Properties

Included F#:
4.5,6,8.5,12,16,25,35,50

Regulatory Compliance

Certificate of Conformance:
[View](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Easy to Order Kits of Our Best Selling Fixed Focal Length Imaging Lenses
 - Full Product Line or Select Focal Lengths Kit Versions Available
 - TECHSPEC **C**, **UC**, and **HP** Imaging Lenses are Also Sold Individually
- TECHSPEC® Imaging Lens Kits provide sets of TECHSPEC C, UC, and HP Imaging Lenses in easy to order kits at a reduced price. These kits offer multiple solutions to applications requiring fixed focal lengths such as factory automation, machine vision, inspection, or rapid prototyping. TECHSPEC Imaging Lens Kits can be ordered as a full product line or as curated selections of focal lengths within the product line. The TECHSPEC C, UC and HP lenses in these kits are C-Mount camera compatible, and feature a locking iris and focus adjustment to prevent unwanted adjustments.
- **C Series**: Compact (C), FALenses for Machine Vision
 - **UC Series**: Ultra-Compact (UC), High Resolution Lenses for Small Sensors
 - **HP Series**: High Performance (HP), C-Mount Lenses for Machine VSION