

VZM 450i 0.5X Extender Lens



Stock #54-670 **CLEARANCE** 1 In Stock

- 1 + ₹6,782

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | ₹6,782 each |
| Need More? | Request Quote |

Product Downloads

General

Lens Accessory **Type:**

Physical & Mechanical Properties

20.00 **Length (mm):**

28.00 **Maximum Diameter (mm):**

Optical Properties

Working Distance Tolerance (mm):

±2

Working Distance (mm):

147.00

Magnification:

0.35X - 2.25X

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

Japan

Imported By:


Edmund Optics India Private Limited

Product Details


- Designed to Accomodate up to 2/3" Sensor Size Formats
- Dependable, Versatile Performance in Compact Designs
- Analog and Digital [Imaging Systems](#) Available

VZM™ Zoom Imaging Lenses enable inspection of a wide range of objects without the inconvenience of changing working distances. In addition, the parfocal zoom allows magnifications to be easily changed without refocusing. These economical lenses are available in working distances ranging from 35mm to 175mm and offer a maximum 2/3" sensor format. Iris versions (i-series) all have locking iris, front filter thread, removable mounting flange, and optional zoom lock. All lenses have a 50mm diameter flange (removable on iris versions except 450i Right Angle) for mounting. VZM™ Zoom Imaging Lenses are ideal for inspection of integrated circuits and solder joints. Also suited for quality control and laboratory inspection needs, as well as surface analysis.

Technical Information



VZM™ 450i



| VZM Model | 100i | 200i | 300 | 300i | 450 | 450i | 600i | 1000 | 1000i |
|---------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|--------------------------|
| Zoom Ratio | 4:1 | 4:1 | 4:1 | 4:1 | 6.4:1 | 6:1 | 6:1 | 4:1 | 4:1 |
| Magnification | 0.25 - 1X | 0.5 - 2X | 0.75 - 3X | 0.75 - 3X | 0.7 - 4.5X | 0.75 - 4.5X | 1 - 6X | 2.5 - 10X | 2.5 - 10X |
| Manual Iris | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> |
| Rotatable Mount | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> |
| Zoom Lock Adapter | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> | | <input type="checkbox"/> | <input type="checkbox"/> | | <input type="checkbox"/> |
| Motorized Version | | | <input type="checkbox"/> | | <input type="checkbox"/> | | | <input type="checkbox"/> | |
| Right Angle Version | | | | | | <input type="checkbox"/> | | | |

| Primary Magnification | With 0.5X Lens | |
|------------------------------|----------------|--------------|
| | Minimum 0.25X | Maximum 1.0X |
| FOV (1/2" Horizontal Sensor) | 24.0mm | 6.0mm |
| Resolution in Object Space | 10 lp/mm | 40 lp/mm |
| Resolution in Image Space | 40 lp/mm | 40 lp/mm |

| | | |
|--------------------------------|-------|-------|
| Working Distance (± 3 mm) | 152mm | 152mm |
|--------------------------------|-------|-------|

| Primary Magnification | With 0.5X Lens | |
|--------------------------------|----------------|---------------|
| | Minimum 0.35X | Maximum 2.25X |
| FOV (1/2" Horizontal Sensor) | 17.6mm | 2.8mm |
| Resolution in Object Space | 12 lp/mm | 80 lp/mm |
| Resolution in Image Space | 34 lp/mm | 35.5 lp/mm |
| Working Distance (± 3 mm) | 147mm | 147mm |

| Primary Magnification | With 0.5X Lens | | With 0.25X Lens | |
|--------------------------------|----------------|---------------|-----------------|----------------|
| | Minimum 0.35X | Maximum 2.25X | Minimum 0.175X | Maximum 1.125X |
| FOV (1/2" Horizontal Sensor) | 17.6mm | 2.8mm | 35.2mm | 5.6mm |
| Resolution in Object Space | 12 lp/mm | 80 lp/mm | 6 lp/mm | 40 lp/mm |
| Resolution in Image Space | 34 lp/mm | 35.5 lp/mm | 34 lp/mm | 35.5 lp/mm |
| Working Distance (± 3 mm) | 147mm | 147mm | 275mm | 275mm |