

[See all 8 Products in Family](#)

Wide Angle $\lambda/4$ Waveplate, 25.4mm Dia. 1064nm



Stock #29-817 **1 In Stock**

MRP ₹2,14,896

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹2,14,896 each
Need More?	Request Quote

Product Downloads

General

Polymer Waveplate **Type:**

Physical & Mechanical Properties

17.8 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

+/- 0.13 **Dimensional Tolerance (mm):**

Optical Properties

±30 **Angle of Incidence (°):**

1064 **Design Wavelength DWL (nm):**

Polymer Film on [N-BK7](#) **Substrate:**

0.5 **Reflection (%):**

$\lambda/4$ **Retardance:**

60-40 **Surface Quality:**

$\leq \lambda/2$ @ 632.8nm **Transmitted Wavefront, RMS:**

$\leq \lambda/250$ @ 0 deg AOI, $\lambda/200$ at 30 deg **Retardance Tolerance:**

≤ 1 arcmin **Beam Deviation (arcmin):**

Threading & Mounting

6.35 **Mount Thickness (mm):**

Environmental & Durability Factors

0 - 40 **Operating Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**

United States **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Up To $\lambda/250$ Retardance Tolerances Out to 30° AOI
- Near Zero-Order Laminated Polymer Construction
- Ideal for Applications with Wide Acceptance Angles

Wide Angle Waveplates are designed to accept a large range of input angles, up to 30° AOI, with minimal retardance shift at non-zero angles of incidence. These waveplates are available with visible or NIR designed wavelengths of 532, 633, 1064 or 1550nm and with $\lambda/2$ or $\lambda/4$ retardance values. Featuring $\leq \lambda/250$ quarter-wave and $\leq \lambda/100$ half-wave retardance accuracies at the center, these waveplates are ideal for applications that require low sensitivity to AOI. Wide Field Waveplates are mounted and constructed with birefringent polymer on a N-BK7 substrate and coated with BBAR coatings.

Note: The fast axis is marked with a line.